

POLAR MATTRESS

1PRMS-002

175 H | 1900 L | 915 W (mm)

Weight: 12kg



KEY FEATURES

- Hygienic wipe-clean surface
- Water-resistant heat welded seams to prevent liquid penetration
 - ideal for incontinence issues and regular cleaning



MATERIAL/FABRICATION

Lightweight, water-resistant, wipe clean exterior offers excellent hygiene properties. Fully heat welded seams used aid water resistance and anti-tamper properties. Interior made from fire retardant, CMHR (combustion modified high resillience) foam is safe for both users and staff

TEST STANDARDS

- Fire retardant to BS 7177:2008 source 5 + A1:2011

OPTIONS

- Some mattresses are available with an integral pillow
- Also available in the following sizes

	Single 2' (915mm)	Small double 4' wide (1220mm)	Double 4'6" wide (1370mm)
5" (125mm) thick	1PRM46-001 125H 1900L 915W (mm)	1PRM46-69-5-C5 125H 1900L 1220W (mm)	1PRM46-69-5-C5 125H 1900L 1370W (mm)
7" (180mm) thick	1PRM46-002 180H 1900L 915W (mm)	1PRM46-69-7-C5 180H 1900L 1220W (mm)	1PRM46-69-7-C5 180H 1900L 1370W (mm)
13" (330mm) thick	1PRM46-001 330H 1900L 915W (mm)	1PRM46-69-13-C5 330H 1900L 1220W (mm)	1PRM46-69-13-C5 330H 1900L 1370W (mm)
21" (530mm) thick	1PRM46-69-21-C5 530H 1900L 915W (mm)	1PRM46-69-21-C5 530H 1900L 1220W (mm)	1PRM46-69-21-C5 530H 1900L 1370W (mm)

COLOUR/FINISH

Cover is Navy Blue as standard

DELIVERY

Lead time is 3 weeks

INSTALLATION/FITTING

No fitting required

MAINTENANCE

For superficial dirt use a disposable wipe and a warm solution of neutral detergent. Do not use abrasive cleaners and disinfect in situ using 0.1% sodium hyperchlorite solution (1000 parts per million chlorine). Avoid the use of biological or phenolic-based cleaners. All cleaning agents and disinfectants must be thoroughly rinsed off and the cover dried before storage or re-use. It is advisable to turn the mattress from top to bottom and side to side on a regular basis to give the foam core a chance to recover and prolong the life of the mattress

WARRANTY

2 year guarantee